


## SPEAr320S expansion board for HMI applications

Data brief

### Features

- 2 x Ethernet RJ45 connectors (ST802RT1A)
- 1x LCD interface for 5.7" 640x480 EDT screen (ET057010DHU)
- 1x Unified LCD interface (EDT displays with Unified interface)
- 1x Resistive touch screen interface (STMPE811)
- 2 x CAN DB9 plug connectors
- 3 x RS232 DB9 plug connectors (ST3232EBTR)
- Onboard temperature sensor and potentiometer (STMPE811)
- 64 Kbit dual interface EEPROM: ISO 15693 and ISO 18000-3 mode 1 compliant contactless interface + I2C (M24LR64)
- 4 Gb NAND flash memory
- I2S stereo audio input and output
- Analog extension connector featuring 8 ADC lines
- General purpose extension connector with GPIOs and I2C functionality
- Unified Power Line modem (PLM) connector
- DC/DC converter L7986A (+24V/+5V)
- MicroSDcard socket
- 3 LEDs
- 2 general purpose buttons
- System reset button



### Description

The EVALSP320SHMI expansion board is intended to be used in conjunction with a SPEAr320S CPU board (sold separately: order code EVALSP320SCPU) to evaluate the SPEAr320S microprocessor with a variety of devices, especially in its HMI automation mode.

## Revision history

**Table 1. Document revision history**

Date	Revision	Changes
16-Jul-2012	1	Initial release

Obsolete Product(s) - Obsolete Product(s)

**Please Read Carefully:**

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

**UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.**

**UNLESS EXPRESSLY APPROVED IN WRITING BY TWO AUTHORIZED ST REPRESENTATIVES, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.**

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2012 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

[www.st.com](http://www.st.com)