


## Automotive SPI to isolated SPI transceiver



LQFP32L  
7x7x1.4 mm


### Product status link

[L9965T, L9965TS](#)

### Product summary

Order code	Package	Packing
L9965T-TR	LQFP32L	Tape and reel
L9965TS-TR		

### Features

- AEC-Q100 qualification ongoing 
- Temperature grade 1: -40 °C to +125 °C operating temperature range
- HBM ESD classification level 2
- CDM ESD classification level C4B
- Full ISO26262 compliant, ASIL-D systems ready, documentation available
- Automatic wake-up of BMS/BMU MCU and PMIC from SHUTDOWN/SLEEP in case of fault detected in the chain
- Single or dual channel p/n in the same package for ring connection
- Up to 59 devices in chain supported
- Cable lengths verified up to 10 meters
- 10 MHz 4-wire SPI interface
- 4 Mbps 2-wire vertical interface (VIF)
- Supports both transformer and capacitive isolation
- Compressed burst data read for enhanced communication speed over the whole chain
- Broadcast write command to configure and control all devices in the chain (or a subset)
- Very low EMI susceptibility and emissions
- Compatible with 3.3 V and 5 V logics
- Supply voltage from 6 V to 24 V

### Application

- Automotive battery monitoring systems
- Energy storage systems
- UPS

### Description

L9965T and L9965TS are bidirectional SPI transceivers that, in a BMS system, allow communication between isolated devices into different voltage domains through a twisted-pair connection.

The devices belong to the L9965 chipset family for high voltage battery management systems monitoring and control.

# 1 Overview

In a high voltage battery management system, the initiator microcontroller accesses the cells monitor and the pack current monitor devices for diagnostics and control purposes. Since the different BMS ICs are located into different voltage domains, it is required isolated communication between each other.


The L9965T/TS allows isolated daisy chain connection through a simple two-wire protocol in L9965x-based HV BMS applications. It converts data from a standard 4-wire SPI protocol to a 2-wire proprietary protocol (and vice versa), supporting the signals isolation by capacitors or transformers.

All the devices in the daisy chain recognize the protocol and can be addressed in read-write mode by a single transceiver. Ring connection can be implemented by the dual channel device L9965T.

L9965T/TS implements two physical communication interfaces:

- SPI target interface
  - This interface is used by the controller MCU to configure and send commands to L9965T/TS and, through it, to all the devices in the chain.
- Isolated Vertical interface (VIF)
  - This interface is typically used to connect BMS daisy-chained devices L9965A/C to L9965T/TS and to each other on the VIF bus.

**Figure 1. L9965T in a L9965x-based BMS system**



The L9965T/TS manages periodic wake-up of the devices in the chain for diagnostic purposes and it is sensitive to fault tones from the devices in the chain when in low power mode. It implements a set of commands to optimize the communication over the chain:

- Broadcast command, to write and configure all devices in the chain (or a subset).
- Burst and compressed burst read, to enable high data rate transmission from all devices in the chain with negligible impact on the power consumption.
- Go-to-sleep command, to move all devices in the chain in low power mode.
- FAULT/WAKEUP tone, to wake-up the chain for normal operation or faults signaling.
- CYCLIC WAKEUP tone, to trigger periodic diagnostic execution in the devices in the chain.

These functionalities are implemented using different functional states, to optimize system power consumption:

- **NORMAL:** full operation mode.
- **CYCLIC WAKEUP/CYCLIC COUNT:** low power modes to send a periodic tone and trigger cyclic diagnostics in the chained devices during low power operation. In these states the device is sensitive to wake-up tones both from the VIF in case of fault and from the SPI by the MCU.

**DEEP SLEEP:** ultra low power state for managing long inactivity periods. In this state the device is sensitive to wake-up tones both from the VIF in case of fault and from the SPI by the MCU.


## 2 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.


### 2.1 LQFP32L (7x7x1.4 mm 5V FULL PLASTIC) package information

Figure 2. LQFP32L (7x7x1.4 mm 5V FULL PLASTIC) package outline

#### BOTTOM VIEW



#### TOP VIEW



**Table 1. LQFP32L (7x7x1.4 mm 5V FULL PLASTIC) package mechanical data**

Symbol	Dimensions in mm		
	Min.	Typ.	Max.
$\theta$	0°	3.5°	7°
$\theta 1$	0°	-	-
$\theta 2$	10°	12°	14°
$\theta 3$	10°	12°	14°
A	-	-	1.60
A1	0.05	-	0.15
A2	1.35	1.40	1.45
b	0.30	0.37	0.45
b1	0.30	0.35	0.40
c	0.09	-	0.20
c1	0.09	-	0.16
D	9.00 BSC		
D1	7.00 BSC		
e	0.80 BSC		
E	9.00 BSC		
E1	7.00 BSC		
L	0.45	0.60	0.75
L1	1.00 BSC		
N	32		
R1	0.08	-	-
R1	0.08	-	0.20
S	0.20	-	-
Tolerance of form and position			
aaa	0.20		
bbb	0.20		
ccc	0.10		
ddd	0.20		

## Revision history

**Table 2. Document revision history**

Date	Version	Changes
10-Sep-2024	1	Initial release.
06-Nov-2024	2	Removed watermark "Restricted".

## Contents

<b>1</b>	<b>Overview .....</b>	<b>2</b>
<b>2</b>	<b>Package information.....</b>	<b>4</b>
<b>2.1</b>	<b>LQFP32L (7x7x1.4 mm 5V FULL PLASTIC) package information .....</b>	<b>4</b>
	<b>Revision history .....</b>	<b>6</b>

**IMPORTANT NOTICE – READ CAREFULLY**

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved