


Reference designs for STM32WL3x microcontrollers



DT73594V1

Designs with different references show different layouts. Picture is not contractual. PCB color may differ.

Features

Includes ST state-of-the-art patented technology

Reference designs

- Fully open hardware platforms
- Suitable for rapid prototyping of end nodes based on Sigfox™, Wireless M-Bus, mioty, and many other proprietary protocols

STM32WL3x microcontroller

- Ultra-low power sub-GHz wireless system-on-chip
- Programmable MCU
- Core: Arm® Cortex®-M0+ 32-bit, running up to 64 MHz
- Program memory: 64-Kbyte, 128-Kbyte, or 256-Kbyte flash memory
- RF transceiver (frequency bands: 159-185 MHz, 413-479 MHz, 826-958 MHz) supporting 2(G)FSK, 2(G)MSK, 4(G)FSK, OOK, ASK, D-BPSK, DSSS modulations
- Low-power autonomous wake-up receiver (LPAWUR)

Oscillators

- 48 MHz HSE (on-board TCXO or XO)
- 32.768 kHz LSE crystal

Connectors

- 2×25 header
- SMA

Supply voltage

- 1.7 V to 3.6 V

Description

The main objective of the STM32WL3x microcontroller reference designs is to recommend a layout and associated BOM for dedicated applications (these boards are not for sale).

These reference designs can be manufactured from files available for download from the www.st.com website. The access to all GPIOs allows the prototyping of a complete application.

Sensitive layout parts can be extracted and pasted in any user board design with the same PCB characteristics and feature set.

The STM32WL3x microcontroller reference designs are provided with the STM32WL3x comprehensive software HAL library. The STM32CubeWL3 MCU Package contains many software examples developed with the STM32WL3x Nucleo-64 boards (NUCLEO-WL33CC1 and NUCLEO-WL33CC2). These examples can be easily adapted for the STM32WL3x microcontroller reference designs.

Using the reference designs to design the user application helps to get the right RF performance and to pass certification.

Product status link

STDES-WL3xxxxx

STDES-WL3C2SLH,
STDES-WL3C2SLL,
STDES-WL3C4EEW,
STDES-WL3C4SHH

1 General information

The STM32WL3x microcontrollers in the STDES-WL3xxxxx reference designs are based on the Arm® Cortex®-M0+ processor.

Note: Arm is a registered trademark of Arm Limited (or its subsidiaries) in the US and/or elsewhere.



2 Main features

- STM32WL3x MCUs
 - Frequency bands: 159-185 MHz, 413-479 MHz, 826-958 MHz
 - Modulations: 2(G)FSK, 2(G)MSK, 4(G)FSK, OOK, ASK, D-BPSK, DSSS
 - Rx sensitivity at 1% BER:
 - -132 dBm at 300 bit/s 169 MHz OOK
 - -132 dBm at 300 bit/s 433 MHz OOK
 - -131 dBm at 300 bit/s 868 MHz 2(G)FSK
 - -112 dBm at 38.4 bit/s 868 MHz 2(G)FSK
 - Transmitter high output power, programmable up to +20 dBm (up to +27 dBm with an external power amplifier only for the 159-185 MHz frequency band)
 - Transmitter medium output power, programmable up to +16 dBm
 - Transmitter low output power, programmable up to +10 dBm
- 2 and 4-layer PCBs supported
- Various frequency ranges supported

3 STM32WL3x microcontroller reference designs and codification

Table 1. STM32WL3x microcontroller reference designs

| Web reference | Board reference | MCU order code | MCU package | Number of layers | SMD, IPD, or external PA | Optimized BOM target |
|----------------|-----------------|----------------|-------------|------------------|--------------------------|----------------------|
| STDES-WL3C2SLH | MB2168 | STM32WL33CCV6 | VFQFPN48 | 2 | SMD | 868 MHz/10 dBm |
| | | | | | | 915 MHz/10 dBm |
| STDES-WL3C2SLL | MB2168 | STM32WL33CCV6 | VFQFPN48 | 2 | SMD | 433 MHz/10 dBm |
| STDES-WL3C4EEW | MB2158 | STM32WL33CCV6A | VFQFPN48 | 4 | SMD, external PA | 169 MHz/27 dBm |
| STDES-WL3C4SHH | MB2218 | STM32WL33CCV6 | VFQFPN48 | 4 | SMD | 915 MHz/20 dBm |

Table 2. STM32WL3x microcontroller reference designs codification

| Example: | STDES- | WL3 | C | 2 | S | L | H |
|--|--------|-----|---|---|---|---|---|
| Device family | | | | | | | |
| STDES- = STMicroelectronics reference design | | | | | | | |
| Wireless products | | | | | | | |
| WL3 = Ultra-low-power long-range STM32WL3x microcontrollers | | | | | | | |
| Wireless microcontroller package | | | | | | | |
| C = VFQFPN48, 48 pins K = VFQFPN32, 32 pins | | | | | | | |
| Reference design number of layers | | | | | | | |
| 2 = 2 layers 4 = 4 layers | | | | | | | |
| Antenna matching and Tx/Rx path connection to the antenna | | | | | | | |
| I = IPD S = SMD E = SMD with external PA controlled by the MCU | | | | | | | |
| Power mode | | | | | | | |
| L = low power (up to +10 dBm) M = medium power (up to +14/16 dBm) H = high power (up to +20 dBm) E = extended range (up to +27 dBm) | | | | | | | |
| Frequency band | | | | | | | |
| W = 159-185 MHz L = 413-479 MHz H = 826-958 MHz | | | | | | | |

4 Hardware layout and configuration

4.1 Schematics and BOM (bill of materials)

A zip file including the following items is available for download:

- Board schematics
- Board Gerber files
- BOMs for selected frequencies and output power

4.2 IPD (integrated passive device)

STMicroelectronics develops integrated passive device (IPD) companion chips for optimized matching, filtering, and balun. The IPD is an all-in-one very compact solution covering the following use cases:

- 10 dBm at 433 MHz
- 16 dBm at 433 MHz
- 16 dBm at 868 MHz
- 20 dBm at 915 MHz

4.3 Output power selection

The reference designs can be tailored to meet the specific output power requirements.

Table 3. Solder bridge configurations

| Output power | SB1 | SB2 |
|----------------|-----|-----|
| Not applicable | OFF | OFF |
| 10 dBm | OFF | ON |
| 14/16 dBm | ON | OFF |
| 20 dBm | ON | ON |

4.4 Radio setting

Depending on the reference design, use the settings indicated in the table below to achieve the best performance for each radio configuration.

Table 4. Radio setting

| Web reference | Optimized BOM target | SMPS level | PA drive mode | PA_LEVEL7 | Degeneration mode |
|----------------|----------------------|------------|---------------|-----------|-------------------|
| STDES-WL3C2SLH | 868 MHz/10 dBm | 1.4 V | TX | 0x53 | ON |
| | | 1.5 V | TX | 0x53 | OFF |
| | 915 MHz/10 dBm | 1.4 V | TX | 0x4F | ON |
| | | 1.4 V | TX | 0x53 | OFF |
| STDES-WL3C2SLL | 433 MHz/10 dBm | 1.4 V | TX | 0x4C | ON |
| | | 1.4 V | TX | 0x53 | OFF |
| STDES-WL3C4EEW | 169 MHz/27 dBm | 1.4 V | TX_HP | 0x35 | OFF |
| STDES-WL3C4SHH | 915 MHz/20 dBm | 2.1 V | TX + TX_HP | 0x53 | ON |

5 Conventions

Table 5. Conventions for solder bridges

| Convention | Definition |
|-----------------------|---|
| Solder bridge SBx ON | SBx connections closed by 0 Ω resistor |
| Solder bridge SBx OFF | SBx connections left open |

Revision history

Table 6. Document revision history

| Date | Revision | Changes |
|-------------|----------|------------------|
| 14-Nov-2024 | 1 | Initial release. |

Contents

| | | |
|------------|---|----------|
| 1 | General information | 2 |
| 2 | Main features | 3 |
| 3 | STM32WL3x microcontroller reference designs and codification | 4 |
| 4 | Hardware layout and configuration | 5 |
| 4.1 | Schematics and BOM (bill of materials) | 5 |
| 4.2 | IPD (integrated passive device)..... | 5 |
| 4.3 | Output power selection | 5 |
| 4.4 | Radio setting | 5 |
| 5 | Conventions | 6 |
| | Revision history | 7 |
| | List of tables | 9 |



List of tables

| | | |
|-----------------|---|---|
| Table 1. | STM32WL3x microcontroller reference designs | 4 |
| Table 2. | STM32WL3x microcontroller reference designs codification. | 4 |
| Table 3. | Solder bridge configurations | 5 |
| Table 4. | Radio setting | 5 |
| Table 5. | Conventions for solder bridges | 6 |
| Table 6. | Document revision history | 7 |

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved