



ST-MCU-FINDER-PC release 6.1.0

Introduction

This release note is updated periodically to keep abreast of ST MCUFinder (ST-MCU-FINDER-PC) evolution, problems, and limitations. Check STMicroelectronics website at www.st.com/en/development-tools/st-mcu-finder-pc.html for the latest version. Refer to [Table 1](#) for the latest release summary.

Table 1. ST-MCU-FINDER-PC 6.1.0 release summary

Type	Summary
Minor release	<ul style="list-style-type: none">Added the possibility to install and upgrade ST-MCU-FINDER-PC without administration rights.

Customer support

For more information or help concerning ST MCUFinder, contact the nearest STMicroelectronics sales office or use the ST community at community.st.com. For a complete list of STMicroelectronics offices and distributors, refer to the www.st.com webpage.

Software updates

Software updates and all the latest documentation can be downloaded from the STMicroelectronics product webpage at www.st.com/en/development-tools/st-mcu-finder-pc.html.



1 General information

1.1 Overview

The ST-MCU-FINDER-PC application allows exploring and connecting to the complete portfolio of STM32 Arm® Cortex®-M, STM32 Arm® Cortex®-A7, and STM8 microcontrollers and microprocessors directly from the developer's desktop environment.

The tool helps the user to:

- Find the MCU, MPU, board part number, or example that best fits the user's application by means of an easy search with multiple criteria
- Have access to MCU, MPU and board technical documentation, key features, and functional block diagrams
- Find STMicroelectronics MCUs and MPUs with features similar to a given STM32, STM8, or competitor product
- Download up-to-date technical documentation for off-line consulting
- Buy on line from STMicroelectronics distributors
- Launch the STM32CubeMX application for the selected STM32 MCU, MPU, or board
- Have access to STM32 social media and ST Community

Note: *Arm is a registered trademark of Arm Limited (or its subsidiaries) in the US and/or elsewhere.*



1.2 Host PC system requirements

Supported operating systems and architectures

- Windows® 10 and 11, 64 bits (x64)
- Linux®: Ubuntu® LTS 22.04 and LTS 24.04, and Fedora® 40
- macOS® 14 (Sonoma), macOS® 15 (Sequoia)

Note: *Windows is a trademark of the Microsoft group of companies.*

Linux® is a registered trademark of Linus Torvalds.

Ubuntu® is a registered trademark of Canonical Ltd.

Fedora® is a trademark of Red Hat, Inc.

macOS® is a trademark of Apple Inc., registered in the U.S. and other countries and regions.

Software requirements

There is no need to install any Java® SE Runtime Environment (JRE™) since version 4.0.0. The ST-MCU-FINDER-PC runs with a bundled JRE™ available inside the downloaded package and no longer with the one installed on the user's machine.

Note: *The bundled JRE™ is Adoptium® Temurin™ 17.0.11 and JavaFX-17.0.11.*

Adoptium and Temurin are trademarks of the Eclipse foundation.

Earlier versions than ST-MCU-FINDER-PC 4.0.0 require a Java® Runtime Environment (JRE™) to execute.

The JRE™ version constraints are:

- 64-bit version mandatory; 32-bit version not supported
- Minimum JRE™ version 17.0.6

The macOS® software requirements are:

- Xcode must be installed on macOS® computers
- Both Xcode and Rosetta must be installed on macOS® computers embedding the Apple® M1 processor

1.3 Setup procedure

1.3.1 Installing ST-MCU-FINDER-PC

To install [ST-MCU-FINDER-PC](#), start by opening the product webpage at www.st.com/en/development-tools/st-mcu-finder-pc.html in an Internet browser and click on **[Get Software]**. After accepting the license terms, follow one of the procedures below depending on the target operating system:

- On Windows®
 1. Choose the ST-MCU-FINDER-PC-Win line
 2. Extract/unzip the `SetupSTMCUFinder-xxx-Win.zip` file
 3. Launch the installation wizard by double-clicking on `SetupSTMCUFinder-xxx-Win.exe`
- On Linux®
 1. Choose the ST-MCU-FINDER-PC-Lin line
 2. Extract/unzip the `SetupSTMCUFinder-xxx-Lin.zip` file
 3. Make sure that access rights are granted to the target installation directory. It is possible to run the installation as root (or sudo) to install ST-MCU-FINDER-PC in shared directories
 4. Enter `chmod 777 SetupSTMCUFinder-xxx` to make the file executable
 5. Double-click on the `SetupSTMCUFinder-xxx` file or launch it from the console window
- On macOS®
 1. Choose the ST-MCU-FINDER-PC-Mac line
 2. Extract/unzip the `SetupSTMCUFinder-xxx-Mac.zip` file
 3. Double-click on the `SetupSTMCUFinder-xxx.app` application file to launch the wizard
 - In case of error, try the following command: `sudo xattr -cr ~/SetupSTMCUFinder-xxx.app`

1.3.2 Uninstalling ST-MCU-FINDER-PC

Uninstalling ST-MCU-FINDER-PC from Windows®

There are three different ways to uninstall ST-MCU-FINDER-PC from Windows®.

- Through the Windows® *Control Panel*:
 - Select Programs and Features from the Windows® *Control Panel* to display the list of programs installed on the computer
 - Right-click **STMCUFinder** and select [**uninstall**]
- From a shell prompt with admin rights, by using the following commands:
 - For ST-MCU-FINDER-PC 4.0.0 and later versions:
 - cd <ST MCUFinder installation path>\Uninstaller
 - uninstall.bat
 - For ST-MCU-FINDER-PC 3.1.0 and earlier versions:
 - java -jar <ST MCUFinder installation path>\Uninstaller\uninstaller.jar
- Through a Windows® *File Explorer* window:
 - For ST-MCU-FINDER-PC 4.0.0 and later versions:
 - Go to the **Uninstaller** folder in ST-MCU-FINDER-PC installation directory
 - Right-click the **uninstall.bat** and select [**run as administrator**]
 - For ST-MCU-FINDER-PC 3.1.0 and earlier versions only:
 - Go to the **Uninstaller** folder in ST-MCU-FINDER-PC installation directory
 - double-click **startuninstall.exe**
 - or
 - double-click the **uninstall** shortcut on the desktop

Uninstalling ST-MCU-FINDER-PC from macOS®

There are two different ways to uninstall ST-MCU-FINDER-PC from macOS®.

- Move **STMCUFinder.app** to the trash
- or
- Use the following command lines:
 - For ST-MCU-FINDER-PC 4.0.0 and later versions:
 - cd <ST-MCU-FINDER-PC installation path>/Uninstaller
 - ./uninstall.sh
 - For ST-MCU-FINDER-PC 3.1.0 and earlier versions:
 - java -jar <ST-MCU-FINDER-PC installation path>/Uninstaller/uninstaller.jar

Uninstalling ST-MCU-FINDER-PC from Linux®

There are two different ways to uninstall ST-MCU-FINDER-PC from Linux®.

- From a shell prompt by launching the uninstall script:
 - For ST-MCU-FINDER-PC 4.0.0 and later versions:
 - cd <ST-MCU-FINDER-PC installation path>/Uninstaller
 - uninstall.sh
 - For ST-MCU-FINDER-PC 3.1.0 and earlier versions:
 - java -jar <ST-MCU-FINDER-PC installation path>/Uninstaller/uninstaller.jar
- From a file explorer:
 - For ST-MCU-FINDER-PC 4.0.0 and later versions:
 - Go to <ST-MCU-FINDER-PC installation path>/Uninstaller
 - Double-click the `uninstall.sh` script
 - For ST-MCU-FINDER-PC 3.1.0 and earlier versions:
 - Go to <ST-MCU-FINDER-PC installation path>/Uninstaller
 - Double-click the start uninstall desktop shortcut

1.4

License

ST-MCU-FINDER-PC is delivered under the [SLA0048](#) software license agreement and its Additional License Terms.

1.5

Cross-selector data disclaimer

The information presented in the cross-reference tool is intended to help the users to narrow their search of STMicroelectronics products based on similarity to other available products. The information is based on data published by other semiconductor manufacturers and might contain errors. STMicroelectronics provides the information "as is" and does not make any representations or warranties as to its accuracy or suitability for any particular purpose. STMicroelectronics recommends that the users make their purchase decision based on their review of STMicroelectronics datasheets and other product documentation. Any pricing information is an estimate for budgetary purposes only.

2 ST-MCU-FINDER-PC 6.1.0 release information

2.1 New features

- Added the possibility to install and upgrade ST-MCU-FINDER-PC without administration rights
- Enhanced the debugging mode using `log4j`

2.2 Fixed issues

Table 2. Main issues fixed in ST-MCU-FINDER-PC 6.1.0

ID	Summary
455	Removed the wrong UART linked to the STM8AF references.
548	STM32CubeMX can now be launched on Linux® from ST MCUFinder even if not installed in the default path.
149320	The issue preventing the data to be refreshed on Windows® 11 is fixed.
158452	The ST community logo is now fully visible.
195569	The STM32CubeMX button allowing to start a new project is enabled when supported.

2.3 Limitations

- The self-upgrade from ST-MCU-FINDER-PC 3.x to 4.0.0 is not supported.
- Example Selector*
 - The feature is functional only for the examples related to the STM32C0 series STM32F4 series, STM32F7 series, STM32G0 series, STM32G4 series, STM32H5 series, STM32H7 series, STM32L0 series, STM32L1 series, STM32L4 series, STM32L4+ series, STM32L5 series, STM32U5 series, STM32WB series, STM32WBA series, and STM32WL series.
 - The feature *Start Project in External IDE* is not available from ST-MCU-FINDER-PC. Run STM32CubeMX to start a project.
 - The “size” of the “Required Software Package” could be unknown when the user selects an example. To get the “size” value, the user must perform the following series of actions:
 - Click on the [Connectivity and data management] button (gear wheel icon)
 - Select the [Check for Update] menu item
 - Click on the [Refresh] button
- The *CAD resources* feature might not be fully functional in the “Use System Proxy parameters” option of the [Updater Settings...]>[Connection Parameters] menu. In the case of an issue, consider selecting the “Manual Configuration of Proxy Server” option instead (or “No Proxy” if the computer running ST-MCU-FINDER-PC has a direct connection to the Internet).

3 Previous releases

3.1 ST-MCU-FINDER-PC 6.0.0 release information

3.1.1 New features

- Added the capability to download all documents for a given part number at once
- Added the possibility to download CAD resources, EDA symbols, footprints, and 3D models
- Added collapsible buttons for all filters, with the possibility to expand or collapse all in filters in one click
- Added the possibility to search easily for a filter
- Added the possibility to reorganize columns in the MCU, MPU, board, and example lists through drag and drop
- Enabled data analytics collection by default
- Enabled the contextual documentation for all peripherals and features of *MCU/MPU Selector* and *Board Selector*
- Added menu option [**Select all/Unselect all columns**] in result list
- Upgraded the bundled JRE™ to Adoptium® Temurin™ 17.0.6 and JavaFX-17.0.2

3.1.2 Fixed issues

Table 3. Main issues fixed in ST-MCU-FINDER-PC 6.0.0

ID	Summary
101209	Fixed the uninstallation of ST-MCU-FINDER-PC under Ubuntu®.
126164	The <i>MCU Selector</i> takes HSPI into account.
137497	Missing documentation is added in [Board Selector]>[Docs] for many boards such as STM320518-EVAL.
142485	The contextual documentation is added for the STM32WBA series.
143461	Massive update for the STM32C0 series with documentation, images, and other.

3.1.3 Limitations

- The self-upgrade from ST-MCU-FINDER-PC 3.x to 4.0.0 is not supported.
- Example Selector*
 - The feature is functional only for the examples related to the STM32C0 series STM32F4 series, STM32F7 series, STM32G0 series, STM32G4 series, STM32H5 series, STM32H7 series, STM32L0 series, STM32L1 series, STM32L4 series, STM32L4+ series, STM32L5 series, STM32U5 series, STM32WB series, STM32WBA series, and STM32WL series.
 - The feature *Start Project in External IDE* is not available from ST-MCU-FINDER-PC. Run STM32CubeMX to start a project.
 - The “size” of the “Required Software Package” could be unknown when the user selects an example. To get the “size” value, the user must perform the following series of actions:
 - Click on the [**Connectivity and data management**] button (gear wheel icon)
 - Select the [**Check for Update**] menu item
 - Click on the [**Refresh**] button
- The *CAD resources* feature might not be fully functional in the “Use System Proxy parameters” option of the [**Updater Settings...>Connection Parameters**] menu. In the case of an issue, consider selecting the “Manual Configuration of Proxy Server” option instead (or “No Proxy” if the computer running ST-MCU-FINDER-PC has a direct connection to the Internet).

3.2 ST-MCU-FINDER-PC 5.0.0 release information

3.2.1 New features

- Added enhancements of the search criteria:
 - organization into categories
 - more accurate commercial product information
 - more specific documentation

3.2.2 Fixed issues

Table 4. Main issues fixed in ST-MCU-FINDER-PC 5.0.0

ID	Summary
57485	The <i>MCU Selector</i> should list USB HS PHY.
92518	[MCUFinder] AES can be checked with series that do not support it.
105359	[MCUFinder] It is possible to add “Reference Buffer” as additional criteria in the <i>MCU Selector</i> ?

3.2.3 Limitations

- The self-upgrade from ST-MCU-FINDER-PC 3.x to 4.0.0 is not supported but the self-upgrade from 4.0.0 to 5.0.0 is supported
- Example Selector*
 - The feature is functional only for the examples related to the STM32C0 series STM32F4 series, STM32F7 series, STM32G0 series, STM32G4 series, STM32H7 series, STM32L0 series, STM32L1 series, STM32L4 series, STM32L4+ series, STM32L5 series, STM32U5 series, STM32WB series, and STM32WL series.
 - The feature *Start Project in External IDE* is not available from ST-MCU-FINDER-PC. Run [STM32CubeMX](#) to start a project.
 - The “size” of the “Required Software Package” could be unknown when the user selects an example. To get the “size” value, the user must perform the following series of actions:
 - Click on the **[Connectivity and data management]** button (gear wheel icon)
 - Select the **[Check for Update]** menu item
 - Click on the **[Refresh]** button
- Under Ubuntu®, automatically uninstalling ST-MCU-FINDER-PC does not work completely. To finalize the uninstallation, the user must delete manually the ST MCUFinder installation path.

3.3 ST-MCU-FINDER-PC 4.0.0 release information

3.3.1 New features

- Added the support for the *Example Selector* that enables example filtering among several parameters
- Added the support for Java® JRE™ bundling
- Added the support for *Favorites* as a filter in **[Export to Excel]** and **Save/Load** search criteria
- Added the support for contextual documentation in *Board Selector*
- Added distinct parameters in *STM32* and *STM8* tabs for the *MCU Results table* popup menus
- Added a splash screen at the launch of the ST MCUFinder

3.3.2 Fixed issues

Table 5. Main issues fixed in ST-MCU-FINDER-PC 4.0.0

ID	Summary
35363	[MCUFinder] [Linux] Bad behavior when scrolling in the <i>MCUList</i> table.

ID	Summary
52510	[all selectors] <i>Data refresh</i> : exit refresh at a first fail.
54269	[all selectors] Only one <i>Set proxy</i> pop-up to be opened in case of wrong proxy.
58526	[MCUFinder] OpenSuse Linux - UI exception when loading ST MCUFinder.
67907	[MCUFinder] Using the [Check/Uncheck All] button for filters has a different effect than selecting elements manually.
69034	[MCUFinder] Non ST PC with no Internet connection: exception when opening a document.
70509	[MCUFinder] After a refresh data, the max and min thumbs filters sliders do not work properly.
75550	[all selectors] The scrollbar does not work properly in small screen.
87392	[MCUFinder][macOS] Bad result table for <i>MCU/MPU Selector</i> .
89700	[all selectors] Display downloaded advertising image instead of default one if available in cache.
98560	[all selectors] Unable to do a reset after activating the [Favorites] button.
98685	[MCUFinder] Canceling a <i>Data Refresh</i> returns an empty MCU list.

3.3.3

Limitations

- No self-upgrade from ST-MCU-FINDER-PC 3.x to 4.0.0
- *Example Selector*
 - The feature is functional only for the examples related to the STM32F4 series, STM32F7 series, STM32G0 series, STM32G4 series, STM32H7 series, STM32L5 series, STM32WB series, and STM32WL series.
 - The feature *Start Project in External IDE* is not available from ST-MCU-FINDER-PC. Run STM32CubeMX to start a project.
 - When the user selects an example, the “size” of the “Required Software Package” could be unknown. To get the “size” value, the user must perform the following series of actions:
 1. Click on the [**Connectivity and data management**] button (gear wheel icon)
 2. Select the [**Check for Update**] menu item
 3. Click on the [**Refresh**] button
- Under Ubuntu®, automatically uninstalling ST-MCU-FINDER-PC does not work completely. To finalize the uninstallation, the user must delete manually the ST MCUFinder installation path.

3.4

ST-MCU-FINDER-PC 3.1.0 release information

3.4.1

New features

Cross Selector extension:

- Side-by-side comparison of a competitor product with approaching STM32 or STM8 products

Easy multi-filter query improvement:

- The cursor remains available after filter selection

3.4.2

Fixed issues

Table 6. Main issues fixed in ST-MCU-FINDER-PC 3.1.0

ID	Summary
40930	Double RMs for STM8L101xx MCUs.
55731	The number of STM8L151M8 GPIO pin is different.
56442	Running STMCUFINDER in 64-bit Linux® (Opensuse).
57004	[CrossSelector] Filters badly displayed after mode switch.
58824	[CrossSelector] Wrong ADC features in cross-selector.

ID	Summary
59239	No SDMMC in peripheral tab at STM32H7.
67313	[McuSelector] Issue when selecting a checkbox: cursor is lost.

3.4.3 Limitations

- Advanced graphic filter not available
- Contextual documentation not available in *Board Selector*
- STM32Cube Expansion Packages such as for artificial intelligence are not available

3.5 ST-MCU-FINDER-PC 3.0.0 release information

3.5.1 New features

- New user interface with flat design and new look and feel
- New *Cross Selector* feature (PC version only):
 - Side-by-side comparison of a reference MCU with approaching MCUs
 - Selection of the relevant comparison criteria and tuning of their respective importance
- Added contextual documentation for any core, Series and peripheral MCU filter

3.5.2 Fixed issues

Table 7. Main issues fixed in ST-MCU-FINDER-PC 3.0.0

ID	Summary
443	STM8 supported IPs: mismatch between MCUFinder and datasheets.
531	When moving sliders: other filters not to be refreshed and cursor lost.
568	Pdf document versions to be displayed.
39197	Keyboard usage to be allowed for Part Number Search.
39794	<i>Board Selector</i> : wrong price for some boards.
40321	Some L462xx MCUs: bad voltage values.
53315	License acceptance to be requested during MCUFinder upgrades.
54278	Load searches display to be enhanced.
54624	STM32L0 Value Line: bad frequency value for L0 Value Line MCUs.
55061	Copy/paste of current MCU selection with ctrl+C and ctrl+V to be supported.
55200	MCUs to be displayed in ascending order.
55319	Sliders (Package/Series...) to be refreshed only after releasing the mouse click.
56281	Wrong name for STM8AF52A8Tx.

3.5.3 Limitations

- Advanced graphic filter not available
- Contextual documentation not available in *Board Selector*

3.6 ST-MCU-FINDER-PC 2.0.1 release information

Corrections

- Ticket 53284 - [ST-MCU-FINDER - Board Selector] All Nucleo-64 and Nucleo-144 boards are missing
 - "Boards Filters" don't contain neither Nucleo-64 nor Nucleo44 type
 - "Boards List" contains no Nucleo-64 or Nucleo-144 boards

Missing boards are: "NUCLEO-F030R8", "NUCLEO-F070RB", "NUCLEO-F072RB", "NUCLEO-F091RC", "NUCLEO-F103RB", "NUCLEO-F207ZG", "NUCLEO-F302R8", "NUCLEO-F303RE", "NUCLEO-F303ZE", "NUCLEO-F334R8", "NUCLEO-F401RE", "NUCLEO-F410RB", "NUCLEO-F411RE", "NUCLEO-F412ZG", "NUCLEO-F413ZH", "NUCLEO-F429ZI", "NUCLEO-F446RE", "NUCLEO-F446ZE", "NUCLEO-F722ZE", "NUCLEO-F746ZG", "NUCLEO-F767ZI", "NUCLEO-H743ZI", "NUCLEO-L053R8", "NUCLEO-L073RZ", "NUCLEO-L152RE", "NUCLEO-L433RC-P", "NUCLEO-L452RE", "NUCLEO-L452RE-P", "NUCLEO-L476RG", "NUCLEO-L496ZG", "NUCLEO-L496ZG-P", "NUCLEO-L4R5ZI"
- Ticket 53488 - [ST-MCU-Finder-PC - MCU Selector] "Core" checklist with mixed case (Arm instead of ARM)
 - "Core" Filters labels are "Arm..." in place of "ARM..."

3.7 ST-MCU-FINDER-PC 2.0.0 release information

New features

- Board availability
 - New board selection tab
 - New board column in the MCUs list. Clicking on a link opens the board view
- Excel table extraction
 - Available for the *Board Selector* and the *MCU Selector*
 - Export to Excel button: outputs an Excel File containing two worksheets
 - Worksheet 1: List of the selected MCUs and boards
 - Worksheet 2: Selected filters
- Favorite part numbers saving and loading for MCUs and boards
 - Save: clicking on the star icon of a part number adds it to the list of favorites
 - Load: clicking on the Favorite icon above the filters loads all favorite part numbers
- Display of similar items (Close selector tool)
 - Display of additional MCUs that do not match exactly the user's criteria
 - A new *Match* column gives the search matching ratio. A match value lower than 100% indicates a MCU that does not entirely match the search criteria such as, for instance, an MCU cheaper than requested.

Revision history

Table 8. Document revision history

Date	Revision	Changes
23-Mar-2018	1	Initial release.
21-Sep-2018	2	Added <i>Chapter 2: ST-MCU-FINDER-PC 2.0.1 release information</i> . Updated <i>Chapter 3: ST-MCU-FINDER-PC 2.0.0 release information title</i> .
11-Dec-2018	3	Added <i>Section 1.3 Setup procedure</i> and <i>Section 1.4 Licensing</i> . Updated the whole document for release 3.0.0, including <i>Section 2 ST-MCU-FINDER-PC 3.0.0 release information</i> .
16-Jul-2019	4	Updated the whole document for release 3.1.0, including <i>Section 2 ST-MCU-FINDER-PC 3.1.0 release information</i> . Added section <i>Cross-selector data disclaimer</i> .
23-Feb-2021	5	Updated the whole document for release 4.0.0, including <i>Section 2 ST-MCU-FINDER-PC 4.0.0 release information</i> , <i>Section 1.2 Host PC system requirements</i> , and <i>Section 1.3 Setup procedure</i> .
23-May-2022	6	Updated the whole document for release 5.0.0, including <i>Section 2 ST-MCU-FINDER-PC 5.0.0 release information</i> , <i>Section 1.2 Host PC system requirements</i> , and <i>Section 1.3 Setup procedure</i> .
31-Jul-2023	7	Updated the whole document for release 6.0.0, including <i>Section 2 ST-MCUFINDER- PC 6.0.0 release information</i> .
21-Nov-2024	8	Updated the whole document for release 6.1.0, including <i>Section 1.3.1: Installing ST-MCU-FINDER-PC</i> and <i>Section 2: ST-MCU-FINDER-PC 6.1.0 release information</i> .

Contents

1	General information	2
1.1	Overview	2
1.2	Host PC system requirements	2
1.3	Setup procedure	3
1.3.1	Installing ST-MCU-FINDER-PC	3
1.3.2	Uninstalling ST-MCU-FINDER-PC	4
1.4	License	5
1.5	Cross-selector data disclaimer	5
2	ST-MCU-FINDER-PC 6.1.0 release information	6
2.1	New features	6
2.2	Fixed issues	6
2.3	Limitations	6
3	Previous releases	7
3.1	ST-MCU-FINDER-PC 6.0.0 release information	7
3.1.1	New features	7
3.1.2	Fixed issues	7
3.1.3	Limitations	7
3.2	ST-MCU-FINDER-PC 5.0.0 release information	8
3.2.1	New features	8
3.2.2	Fixed issues	8
3.2.3	Limitations	8
3.3	ST-MCU-FINDER-PC 4.0.0 release information	8
3.3.1	New features	8
3.3.2	Fixed issues	8
3.3.3	Limitations	9
3.4	ST-MCU-FINDER-PC 3.1.0 release information	9
3.4.1	New features	9
3.4.2	Fixed issues	9
3.4.3	Limitations	10
3.5	ST-MCU-FINDER-PC 3.0.0 release information	10
3.5.1	New features	10
3.5.2	Fixed issues	10
3.5.3	Limitations	10
3.6	ST-MCU-FINDER-PC 2.0.1 release information	11
3.7	ST-MCU-FINDER-PC 2.0.0 release information	11

Revision history	12
List of tables	15

List of tables

Table 1.	ST-MCU-FINDER-PC 6.1.0 release summary	1
Table 2.	Main issues fixed in ST-MCU-FINDER-PC 6.1.0	6
Table 3.	Main issues fixed in ST-MCU-FINDER-PC 6.0.0	7
Table 4.	Main issues fixed in ST-MCU-FINDER-PC 5.0.0	8
Table 5.	Main issues fixed in ST-MCU-FINDER-PC 4.0.0	8
Table 6.	Main issues fixed in ST-MCU-FINDER-PC 3.1.0	9
Table 7.	Main issues fixed in ST-MCU-FINDER-PC 3.0.0	10
Table 8.	Document revision history	12

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved