


Battery holder for cylindrical batteries and battery management system node for automotive applications



Features

- 14-slot battery holder for cylindrical INR 18650 battery cells (not included)
- All batteries are connected in series
- Proper housing for the [AEK-POW-BMS63EN](#), [AEK-POW-BMSWTX](#) and [AEK-POW-BMSNOTX](#) evaluation boards BMS node (not included)
- Easy battery removal supported by a satin ribbon
- Low-side current sensing through an external resistor included in the package a 100 mΩ, 10 W resistor
- Five NTC thermistors (included)
- Stackable kit to build a compact battery pack (mechanical parts included)
- Dimensions 425 x 120 x 52 mm
- Included in the [AutoDevKit](#) ecosystem

Description

The battery management system (BMS) is a fast-growing application pervading several fields of the electronic industry including automotive and industrial markets.

To support fast evaluation and meet stringent time-to-market for BMS solutions, the AutoDevKit ecosystem has been extended to include a specific cylindrical battery holder.

The purpose of this extension is to quickly create a battery pack to evaluate ST BMS solution based on the [AEK-POW-BMS63EN](#) analog front end node hosting the [L9963E](#) and the [AEK-COM-ISOSPI1](#) ISOSPI transceiver hosting the [L9963T](#).

You can test the battery pack also using our latest BMS evaluation boards: [AEK-POW-BMSWTX](#) and [AEK-POW-BMSNOTX](#).

The [AEK-POW-BMSHOLD](#) battery holder contains a maximum of 14 cells, all connected in series, and a dedicated slot and connector for our range of BMS evaluation boards.

To build a complete battery pack in both centralized or dual-ring topologies, you can stack up to three / four [AEK-POW-BMSHOLD](#) kits (the limit is the stackable weight). A separate bag inside the kit package contains six M3x12 mm pan steel screws, four M3x25 mm plus six M3x30 mm hexagonal steel spacers. These elements can be used to mount another [AEK-POW-BMSHOLD](#) layer.

The [AEK-POW-BMSHOLD](#) has a long satin ribbon tied to a buttonhole on the plexiglass used to support easy battery removal.

The internal wiring of the featured 4-pole mammoth connector allows adding a sensing resistor between pin 2 and pin 3. Pin 1 and pin 4 are, respectively, the positive and the negative terminals of the mockup. For demo purposes, a 100 mΩ, 10 W, ±1% precision resistor is included in the kit package.

The [AEK-POW-BMS63EN](#) node boards have to be connected to the crimped central connector provided in the [AEK-POW-BMSHOLD](#) kit.

The connector is organized as follows: pin 1 is the cell VBAT, pin 2 to 16 are dedicated to the battery connections, pins 17 and 18 are ext Ground, pins 19 and 20 are ISenseP and ISenseM, pins 21 to 30 are dedicated to NTCs for temperature sensing.

Product summary	
Battery holder for cylindrical batteries and battery management system node for automotive applications	AEK-POW-BMSHOLD
Automotive chip for battery management applications with daisy chain up to 31 devices	L9963E
Battery management system module based on L9963E	AEK-POW-BMS63EN
Battery management system module based on the L9963E and L9963T	AEK-POW-BMSWTX
Non-isolated Battery Management node	AEK-POW-BMSNOTX
SPI to isolated SPI dongle based on the L9963T transceiver	AEK-COM-ISOSPI1
Automotive general purpose SPI to isolated SPI transceiver	L9963T
AutoDevKit Studio for 32-bit power architecture MCUs	STSW-AUTODEVKIT
Application	Automotive Battery Management System (BMS)


The even numbers with yellow cables are NTC-, whereas the odd numbers with blue cables are NTC+. Five 10 k Ω , $\pm 1\%$ tolerance NTC thermistors are provided in the kit.

The AEK-POW-BMSHOLD kit supports INR 18650 battery type. The estimation of SoC and SoH included in AutoDevKit Studio is computed through an extended kalman filter with characterization data coming from INR 18650 MJ1 batteries by LG.

Note: For further information on our range of BMS evaluation boards, refer to the board related page on www.st.com and to [UM3185](#).


1 Block diagram

Figure 1. Block diagram



The image above shows the block diagram of connections between the battery holder and the BMS evaluation board when using an AEK-POW-BMS63EN.


Figure 2. Stacked layers



2 How to use the AEK-POW-BMSHOLD

Step 1. Connect the BMS evaluation board to the battery holder through the dedicated connector.

Figure 3. BMS evaluation board connection to the battery holder



Step 2. Use the screws included in the pack to anchor the board to the mockup.

Step 3. Place the batteries in the dedicated slot.

Note: The cell number goes from 1 to 14 (from the board downwards to the end of the mockup).

Important:

Pay attention to the polarity indicated on the plexiglass to avoid short-circuits.

Place the satin ribbon under the batteries to remove them easily.


Step 4. Optionally, you can use the flying cables to connect the NTCs included in the pack.
After connecting one or more NTCs to the positive and negative cables, you can place them on the batteries to sense the cell temperatures.
Cell voltage varies according to the external temperature variations. Voltages are indicated in the characterization curve of the component datasheet (Vishay, PN NTCALUG02A103F).

Figure 4. Cables to connect external NTCs




- Step 5.** The battery holder could also be used to supply an external load, such as a motor, a lamp, LEDs, etc. For this scope, connect the resistor (included in the pack) to the mammoth connector. Then, connect the positive and negative cables to the load as indicated on the plexiglass.

Figure 5. Connection scheme



The maximum current allowed is 10 A. You could connect another resistor to absorb more current.

Figure 6. Connecting the resistor to the mammoth connector



Revision history

Table 1. Document revision history

Date	Revision	Changes
11-Sep-2023	1	Initial release.
26-Sep-2024	2	Updated Features, Product Summary, Description, Section 1: Block diagram and Section 2: How to use the AEK-POW-BMSHOLD .

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved