

TSC2020, TSC2021, TSC2022

Datasheet

100 V, precision, bidirectional current sense amplifier





TSSOP8

Maturity status link

TSC2020, TSC2021, TSC2022

Features

- Wide common-mode voltage: -4 to 100 V
- High common-mode rejection CMR: 100 dB min.
- Offset voltage: ±150 µV max.
- Offset drift: 0.5 µV/°C max.
- Enhanced PWM rejection
- 2.7 to 5.5 V supply voltage
- Internal fixed gain
 - TSC2020: 20 V/V
 - TSC2021: 50 V/V
 - TSC2022: 100 V/V
- Gain error: 0.3% max.
- Gain drift: 3.5 ppm/°C max.
- SO8, MiniSO8 and TSSOP8 packages
- AEC-Q100 qualified

Applications

•

- High-side/low-side current sensing
- Battery management system
- 48 V power distribution
- 48 V power tools
- Motor control
- Automotive

Description

TSC2020, TSC2021 and TSC2022 are a series of precision bidirectional current sense amplifier. They can sense current via a shunt resistor over a wide range of common-mode voltages, from -4 to +100 V, whatever the supply voltage is. It is able to sense very low drop voltages, minimizing measurement error.

TSC2020, TSC2021 and TSC2022 are current sense amplifiers that may be used for various functions like precision current measurement, overcurrent protection, current monitoring, and feedback loops. These devices fully operate over the supply voltage range of 2.7 to 5.5 V, and over an ambient temperature range of -40 to 125 $^{\circ}$ C.



1 Block diagram and pin description



Figure 2. Pin connections (top view)



Table 1. Pin description

SO8/MiniSO8	TSSOP8	Pin name	Description
1	3	IN-	Negative input
2	4	GND	Ground
3	6	VREF2	Reference voltage 2
4	1	NC	Not connected
5	8	OUT	Output
6	5	VCC	Supply voltage
7	7	VREF1	Reference voltage 1
8	2	IN+	Positive input



2

Absolute maximum ratings and operation conditions

Symbol	Parameter	Value	Unit
V _{CC}	Supply voltage (1)	-0.3 to 5.8	V
V _{ICM}	Common-mode voltage on input pins	-10 to 105	V
V _{DIF}	Differential voltage between input pins (IN+, IN-)	±70	V
V _{REF1} , V _{REF2} , V _{OUT}	Voltage present on pins REF1, REF2, and OUT	GND - 0.3 to V _{CC} + 0.3	V
TJ	Junction temperature	150	°C
T _{STG}	Storage temperature	-65 to 150	°C
	Human body model (HBM) (2)	2000	V
ESD	Charged device model (CDM) ⁽³⁾ SO8 MiniSO8 TSSOP8	750 1000 500	V
RTH _{JA}	Thermal resistance junction to ambient ⁽⁴⁾⁽⁵⁾ SO8 MiniSO8 TSSOP8	125 190 120	°C/W

Table 2. Absolute maximum ratings

1. All voltage values, except the differential voltage, are with respect to the network ground terminal.

2. According to JEDEC standard JESD22-A114F.

3. According to ANSI/ESD STM 5.3.1.

- 4. Short-circuits can cause excessive heating and destructive dissipation.
- 5. The RTHs are typical values.

Table 3. Operating conditions

Symbol	Parameter	Value	Unit
V _{CC}	Supply voltage	2.7 to 5.5	V
V _{ICM}	Common-mode voltage on input pins	-4 to +100	V
V _{REF}	Output offset adjustment range	0 to V _{CC}	V
т	Operating free-air temperature range	-40 to 125	°C



3 Electrical characteristics

Table 4. Electrical characteristics - V_{CC} = 2.7 V, V_{ICM} = 48 V, T = 25 °C (unless otherwise specified).

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit	
Power supply							
		V _{ICM} = -4 to 100 V		1.7	2.3		
ICC	Current consumption	Tmin < T < Tmax			2.3	mA	
Input	1				1		
		V _{ICM} = 12 V, V _{REF} = 1.35 V			150		
I) (a a l		Tmin < T < Tmax			200	μV	
Vos	Onset voltage (RTI)	V _{ICM} = 48 V, V _{REF} = 1.35 V			400		
		Tmin < T < Tmax			500		
		V _{ICM} = 12 V, Tmin < T < Tmax			0.5	uV/°C	
ΔVos/Δ1	Offset drift vs. temperature	V _{ICM} = 48 V, Tmin < T < Tmax			1	μv/°C	
0145		V _{ICM} = - 4 to 100 V, DC mode	100	112		dP	
CMR	Common-mode rejection	Tmin < T < Tmax	100			aв	
		V _{ICM} = 12 V, Vsense = 0		100	130		
	land the second second	Tmin < T < Tmax			140		
IIB	Input bias current	V _{ICM} = 48 V, Vsense = 0		200	230	μΑ	
		Tmin < T < Tmax			240		
	Vsense operating range with Eg $\leq 0.3\%$ ⁽²⁾	TSC2020			123.8	mV	
		Tmin < T < Tmax			123.6		
IVeeneel		TSC2021			49.1		
Ivsensel		Tmin < T < Tmax			48.8		
		TSC2022			24.1		
		Tmin < T < Tmax			23.9		
Output							
		TSC2020		20			
G	Gain	TSC2021		50		V/V	
		TSC2022		100			
		TSC2020					
		ΔV_{OUT} = 100 mV to (V _{CC} - 100 mV)		0.01	0.3		
Fa	Gain arror	Tmin < T < Tmax			0.35	0/_	
⊏y	Gainenoi	TSC2021, TSC2022				70	
		ΔV_{OUT} = 100 mV to (V _{CC} - 100 mV)		0.01	0.4		
		Tmin < T < Tmax			0.4		
ΔEg/ΔT	Gain error drift	Tmin < T < Tmax			3.5	ppm/°C	
NLE	Linearity error	V _{ICM} = - 4 to 100 V		0.01		%	
		Isource = 0.2 mA		11	25		
Veo Ver	Drop voltage output high	Tmin < T < Tmax			35		
VCC - VOH	וסים voitage output nign	Isource = 2 mA		115	150	mV	
		Tmin < T < Tmax			200		



Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit	
		lsink = 0.2 mA		24	40		
Max	Output voltage low	Tmin < T < Tmax			55	m\/	
VOL		Isink = 2 mA		200	240		
		Tmin < T < Tmax			390		
		Sink mode	8	12.5	18	mA	
lour	Output ourropt	Tmin < T < Tmax	5		24		
1001	Output current	Source mode	10	14.5	25	IIIA	
		Tmin < T < Tmax	5		30		
Reg Load	Load regulation	I_{OUT} = -5 to +5 mA		0.2	1.5	$\frac{mV}{mA}$	
CL	Maximum capacitive load	No sustained oscillation		1		nF	
Offset adjustn	nent	I			1		
RT	V _{REF} gain	$\text{OUT/V}_{\text{REF}}$ gain for either V_{REF} pin		0.5		V/V	
Acc	Accuracy, RT	One V_{REF} pin connected to $V_{\text{CC}},$ the other to GND		0.2		%	
Dynamic perfo	ormances	·			1		
DW	Small signal -3 dB bandwidth	R_L = 10 k Ω , C_L = 100 pF	350	650		kU7	
DVV		Tmin < T < Tmax	350			KHZ	
		C _L = 100 pF					
		TSC2020, Vsense = 108 mV	1.1	1.8			
		TSC2020, Tmin < T < Tmax	1				
SR	Slew rate	TSC2021, Vsense = 43 mV	1.5	2.4		V/µs	
		TSC2021, Tmin < T < Tmax	1.4				
		TSC2022, Vsense = 22 mV	1.9	3			
		TSC2022, Tmin < T < Tmax	1.8				
E _N	Spectral density (RTI) (1)	f = 1 kHz		63		nV/√Hz	

1. RTI stands for "Related to input."

2. Vsense = (Vin+) – (Vin-).



Table 5. Electrical characteristics - V_{CC} = 5 V, V_{ICM} = 48 V, T = 25 °C (unless otherwise specified).

Symbol	Parameter	Conditions Min. Typ		Тур.	Max.	Unit	
Power supply				-			
		V _{ICM} = -4 to 100 V		1.8	2.4		
ICC	Current consumption	Tmin < T < Tmax			2.4	mA	
Input					1		
		V _{ICM} = 12 V, V _{REF} = 2.5 V			150	μV	
Vos	Offect veltere (DTI) (1)	Tmin < T < Tmax			200		
	Onset voltage (RTI)	V _{ICM} = 48 V, V _{REF} = 2.5 V			400		
		Tmin < T < Tmax			500		
		V _{ICM} = 12 V, Tmin < T < Tmax			0.5		
ΔVOS/Δ1	Offset drift vs. temperature	V _{ICM} = 48 V, Tmin < T < Tmax			1	μν/-Ο	
CMP	O management of the section of the s	V _{ICM} = -4 to 100 V, DC mode	100	112			
CMR	Common-mode rejection	Tmin < T < Tmax	100			aв	
SVR	Cumplu veltage rejection	V _{CC} = 2.7 to 5.5 V	100	118			
SVR	Supply voltage rejection	Tmin < T < Tmax	100			QВ	
		V _{ICM} = 12 V, Vsense = 0		100	130		
	Input bias current	Tmin < T < Tmax			140		
IB		V _{ICM} = 48 V, Vsense = 0		200	230	μΑ	
		Tmin < T < Tmax			240		
	Vsense operating range with Eg \leq 0.3% ⁽²⁾	TSC2020			238.5		
		Tmin < T < Tmax			238.2	mV	
Vsense		TSC2021			94.9		
Vocnoc		Tmin < T < Tmax			94.7		
		TSC2022			47.1		
		Tmin < T < Tmax			46.8		
Output				1	1	1	
		TSC2020		20			
G	Gain	TSC2021		50		V/V	
		TSC2022		100			
		TSC2020		0.01	0.3		
		$\Delta v_{OUT} = 100 \text{ mV}$ to ($v_{CC} - 100 \text{ mV}$)			0.35		
Eg	Gain error				0.00	%	
		15C2021, 15C2022		0.01	0.4		
		$\Delta v_{00} = 100 \text{ mV} \text{ to } (v_{CC} - 100 \text{ mV})$			0.4		
	Coin orror drift				2.5	nnm/°C	
				0.01	3.5		
INLE				0.01	05	70	
		Isource = 0.2 mA		18	35		
V _{CC} - V _{OH}	Drop voltage output	$\frac{11001 \times 1 \times 100000}{1000000000000000000000000000000$		100	40	mV	
		Tmin < T < Tmax		122	210		
			1	1			



Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit	
		lsink = 0.2 mA		35	50		
V _{OL}	Outrast with an low	Tmin < T < Tmax			70	m\/	
	Output voltage low	Isink = 2 mA		217	250		
		Tmin < T < Tmax		400			
		Sink mode	8	13.5	20	mA	
Голт		Tmin < T < Tmax	5		24		
1001	Output current	Source mode	10	14.5	25	IIIA	
		Tmin < T < Tmax	5		30		
Reg load	Load regulation	I _{OUT} = -5 to +5 mA		0.2	1.5	$\frac{mV}{mA}$	
Offset adjustn	nent						
RT	V _{REF} gain	$\text{OUT/V}_{\text{REF}}$ gain for either V_{REF} pin		0.5		V/V	
Acc	Accuracy, RT	One V_{REF} pin connected to $V_{\text{CC}},$ the other to GND		0.2		%	
Dynamic perfe	ormances	·		•	,	'	
	Small signal 2 dD bandwidth	$R_L = 10 \text{ k}\Omega, C_L = 100 \text{ pF}$	450	700			
DVV	Smail signal -3 dB bandwidth	Tmin < T < Tmax	450			KHZ	
		C _L = 100 pF					
		TSC2020, Vsense = 200 mV	1.4	2			
		TSC2020, Tmin < T < Tmax	1.2				
SR	Slew rate	TSC2021, Vsense = 80 mV	1.7	2.8		V/µs	
		TSC2021, Tmin < T < Tmax	1.6				
		TSC2022, Vsense = 40 mV	2.4	3.9			
		TSC2022, Tmin < T < Tmax	2.2				
EN	Spectral density (RTI) ⁽¹⁾	f = 1 kHz		53		nV/√Hz	

1. RTI stands for "Related to input."

2. Vsense = (Vin+) – (Vin-).



Typical characteristics 4

TSC2020 is used for typical characteristics, unless otherwise specified.





Figure 4. Gain error production distribution



Population









Figure 10. Input bias current vs. temperature



Figure 12. Input bias current vs. Vsense





















Figure 22. Linearity vs. Vsense with V_{CC} = 5.5 V



























Figure 34. Large signal response with V_{CC} = 5 V







57/

















Figure 44. CMRR vs. frequency















5 Application information

5.1 Overview

The TSC202x family is a current sense amplifier specially designed to accurately measure current by amplifying the voltage across a shunt resistor connected to its input. It is a zero-drift topology, allowing to reach a high CMRR level of 100 dB min. and a high level of input offset voltage of 200 µV at 12 V common mode voltage and over temperature.

Multiple fixed gain versions are available (x20, x50, x100) for design optimization. Thanks to the use of a thin film resistor, the TSC202x offers an extremely precise gain and very high CMRR performance even in a high frequency range. Moreover, there is the possibility to fix the output common mode voltage, allowing the TSC202x to be either used as a unidirectional or bidirectional current sensing amplifier.

The TSC202x provides an extended input common range from -4 V below negative supply voltage, and up to 100 V, allowing either low-side or high-side current sensing, while TSC202x devices can operate from 2.7 to 5.5 V.

The TSC202x embedded a system to optimize the PWM rejection, allowing to reduce the effect of fast input common mode voltage variation on the output signal.

The parameters are very stable in the full VCC range, and several characterization curves show the TSC2020 device characteristics at 2.7 V and 5.0 V. Additionally, the main specifications are ensured in extended temperature ranges from -40 to 125 °C.

5.2 Theory of operation

The main particularity of the TSC202x is the ability to work with a wide input common mode voltage. It is an excellent device to work with a 48 V application as the TSC202x can support and measure the current online at a voltage up to 100 V without any additional protective components. It is also a good candidate for use in a low-side configuration. And thanks to its ability to work with a negative common mode voltage down to -4 V, it can support, without any additional protection, fast current variation into a shunt, which is always a bit inductive. The TSC202x family embedded a PWM enhancer, allowing it to be used in applications dealing with fast variation of input common mode voltage as motor control or solenoid valve. Its good DC performance makes the TSC202x an excellent device to measure accurately the current. Figure 52. Functional block diagram depicts a global overview of the TSC202x.

Figure 52. Functional block diagram





5.3 PWM enhancer

The TSC202x current sensing integrates a detection of transient signal on the input common bus to reduce the impact of such an event on the output pin. Such large $\Delta V/\Delta T$ common mode signals are commonly seen in applications such as motor control when the current sensing is used in inline sensing. See Figure 70 or solenoid drive. Figure 53. Output response to large $\Delta V/\Delta T$ input common mode signals shows the TSC2020 output voltage response where the input pins are submitted to a 20 kHz PWM with 0 - 48 V amplitude.





The output impact to a fast input common mode variation is typically limited to hundreds mV during less than 3 µs, allowing it to work with a wide range of PWM duty cycle conditions in control motor applications.



5.4 Unidirectional / bidirectional operation

The TSC202x output common mode voltage level can be set thanks to voltages applied on the Vref1 and Vref2 pins. These two pins to set the device either in bidirectional or in unidirectional operation. The voltage applied on those pins must not exceed the V_{CC} range. There is no difference between both reference pins; the voltage can be applied to either one pin or the other without distinction.

Unidirectional operation

Unidirectional mode of operation allows the device to measure the current through a shunt resistor in one direction only. The output reference can be ground or V_{CC} and can be set by using the Vref1 and Vref2 pins for adjustment.

Ground referenced



Figure 54. Output referenced to ground

In the configuration described in Figure 54. Output referenced to ground, both the Vref1 pin and Vref2 pin are connected to the ground. The output common mode voltage is then automatically set to Gnd and the output voltage can be expressed as equation (1).

$$Vout = (IN_{+} - IN_{-})^{*}Gain \tag{1}$$

This configuration allows the full-scale output in unidirectional mode. It allows to measure a current flowing into the shunt from IN+ to IN-.



V_{CC} referenced



Figure 55. Output referenced to V_{CC}

In the configuration described in Figure 55. Output referenced to V_{CC} , the Vref1 pin and Vref2 pin are connected to the V_{CC} power supply. The output common mode voltage is then automatically set to V_{CC} voltage and the output voltage can be expressed as equation (2):

$$Vout = (IN_{+} - IN_{-})^{*}Gain + Vcc$$
⁽²⁾

This configuration allows the full-scale output in unidirectional mode to measure a current flowing into the shunt from IN- to IN+.

Bidirectional operation

Bidirectional mode of operation allows the device to measure currents through a shunt resistor in two directions. The output reference can be set anywhere within the power supply range. If the output common mode voltage is set at mid-range, the full-scale current measurement range is equal in both directions. This is achieved by connecting one Vref pin to VCC and the other Vref pin to Gnd as described in Figure 56. Split supply.

Split supply



Figure 56. Split supply

•

The significant advantage of this configuration is that the TSC202x can be used in bidirectional mode with an output common mode voltage set at the middle of the scale, with an accuracy of 0.2%, without any added external component or power supply. This configuration allows to create a mid-scale offset ratiometric to the power supply. The output voltage can be expressed as equation (3):

$$Vout = (IN_{+} - IN_{-})^{*}Gain + \frac{Vref1 + Vref2}{2}$$
(3)

External with a reference voltage





It can be done by connecting both Vref pins to a voltage reference as described in Figure 57. External supply. Users can set the output in a non-symmetrical configuration, adjusting Vref according to user needs. In this configuration, the Vref1 pin and Vref2 pin are connected to an adjustable reference voltage TS431. The output common mode voltage is then automatically set to the reference voltage when no current flows through the Rshunt resistance.

The output voltage can be expressed as equation (4).

$$Vout = (IN_{+} - IN_{-})^{*}Gain + Vref$$
⁽⁴⁾

External with a divider bridge

It is recommended to buffer the resistor divider as depicted in Figure 58. Recommended schematic thanks to a precise op amp such as the TSV711.



Figure 58. Recommended schematic



The output voltage can be expressed as equation (6)

$$Vout = (IN_{+} - IN_{-})^{*}Gain + Vcc^{*}\frac{Rb}{Ra + Rb}$$
⁽⁵⁾

When the output common mode voltage is supplied by an external power supply, to improve the output voltage measurement, it is recommended to measure the V_{out} differentially with respect to V_{ref} voltage. It provides the best CMRR measurement, the best noise immunity, and a more accurate V_{out} voltage. A decoupling capacitance of 1 nF minimum can be also added to better filter the power supply.

5.5 RSENSE selection

The selection of the shunt resistor is a tradeoff between dynamic range and power dissipation. Generally, in high current sensing applications, the focus is to reduce the power dissipation (RI²) as much as possible by choosing the smallest value of shunt as $Rsense \leq \frac{Pmax}{Imax^2}$.

In low current applications the Rsense value could be higher, to minimize the impact of the offset voltage of the circuit on the accuracy measurement.

The tradeoff is mainly when a dynamic range of current to measure is large, meaning the ability to measure with the same shunt value low current to high current. Generally, the current full-scale (Imax-Imin) defines the shunt value thanks to the full output voltage range and the TSC202x gain. The TSC202x offers the possibility to work with full-scale ΔV_{out} = 100 mV to V_{cc} - 100 mV with maximum gain accuracy of 0.3%.

At first order, the full current range to measure through Rsense can be defined by equation 7, just by taking the gain error and input offset voltage as inaccuracy parameters:

$$Isense_full_scale^*Rsense = \frac{Vcc - 200mV}{TSC_Gain(1 + Eg)} - Vio$$
(6)

Figure 59. Tradeoff between shunt resistance, power dissipation, and accuracy shows an example of the tradeoff between power dissipation and accuracy for the TSC2020 current sensing. It is considered a current to measure from 1 A to 10 A through different shunt values from 10 m Ω up to 50 m Ω . The maximum current (10 A) gives an idea of the worst-case power dissipation expected, whereas the lowest current (1 A) gives a first order idea of the error that can be expected on the output.

Figure 59. Tradeoff between shunt resistance, power dissipation, and accuracy







5.6 Input offset voltage drift over temperature

The maximum input offset voltage drift over temperature is defined as the offset variation related to the offset value measured at 25 °C. The signal chain accuracy at 25 °C can be compensated during production at application level. The maximum input voltage drift over temperature enables the system designer to anticipate the effect of temperature variations.

The maximum input voltage drift over temperature is computed using equation 8.

$$\frac{\Delta V_{io}}{\Delta T} = \max \left| \frac{V_{io}(T) - V_{io}(25^{\circ}C)}{T - 25^{\circ}C} \right|$$
(7)

Where T = -40 $^{\circ}$ C and 125 $^{\circ}$ C.

The TSC202x datasheet maximum value is guaranteed by measurements on a representative sample size ensuring a C_{pk} (process capability index) greater than 1.3.

5.7 Error calculation

The principal source of error such as input offset voltage, gain error, common mode rejection ratio, are described separately in the electrical characteristics. This section summarizes the most important error to consider during a design phase.

Input offset voltage error

Equation 9 depicted a first order error calculation just by considering the input offset voltage. In a temperature environment, also taken into consideration is the deviation of the Vio and the error linked to the input offset on the output voltage can be written as equation 9.

$$Vio \ Error = (\pm Vio \pm \Delta Vio / \Delta T)^* Gain$$
(8)

Gain error and shunt resistance accuracy

$$Gain \, error = Gain(1 + \varepsilon gain) \tag{9}$$

$$Rsense\ error = Gain(1 + \varepsilon Rsense) \tag{10}$$

Where $\epsilon gain$ is the gain error 0.35% max. for the TSC202x.

Where ϵ Rsense is the shunt resistance error. Shunt resistors from 5 m Ω to 100 m Ω are available with 1% accuracy or better.

CMR error

In the electrical characteristics CMR is specified at one input common mode voltage. So, in order to take into consideration the variation of the input voltage offset depending on the Vicm, the calculus must be done till this known point. Let us take the V_{icm} = 12 V as a reference point.

Therefore, the error on V_{out} due to a common mode voltage variation can be written as equation 12:

$$CMR \ error = \pm \frac{Vicm - 12V}{CMR} * Gain \tag{11}$$

Output common mode error

This error can be considered when the output common mode voltage is set as suggested in Figure 60. Schematic for V_{ocm} error, and so by using the internal divider bridge. Otherwise, it is important to consider the error linked to the voltage source applied on the Vref1 pin and Vref2 pin.

Figure 60. Schematic for Vocm error



The divider bridge is made by two resistances of 50 k Ω given an output common mode voltage of $\frac{Vref1 + Vref2}{2}$. Due to a small mismatch of the internal resistance, the error on the output common mode voltage can be described as equation 13:

$$Vocm = \left(\frac{Vref1 + Vref2}{2}\right). (1 + \varepsilon Acc)$$
(12)

Where εAcc is the accuracy referred to the output with a typical value of 0.2%.

Noise

Figure 48 expresses the TSC2020 noise referred to input. This device shows that only a white noise density is 53 nV / \sqrt{Hz} , overall TSC2020 bandwidth.

Considering that there is no additional filter on the TSC2020 and it is only bandwidth limited, it can be considered that at over 700 kHz, there is an attenuation of the noise with a first order filtering. So, the equivalent noise

bandwidth is 700kHz. $\frac{\pi}{2}$.

The RMS value of the output noise is the integration of the spectral noise over the bandwidth of interest and can be expressed as equation 14:

$$enRMS = \left(\sqrt{\int_{0.1}^{700000.\frac{\pi}{2}} (53.10^{-9})^2 df}\right)^* Gain$$
(13)

Total error

The maximum total error expected on the output of the device can be considered as the sum of the different source described just above by considering all the maximum parameters of the datasheet. This approach is very pessimistic, and the chance to obtain all the maximum parameter values on a same die is extremely low, even null. To have a good picture of the maximum possible error on the output, total error can be determined by using a simplified statistical approach as the root-sum-of-the-squares (RSS), a method to combine the error terms. So, the error can be written as equation 15.

$$Error_Rss = \sqrt{\left(\varepsilon G\right)^2 + \left(\frac{Vio}{Rshunt.I}\right)^2 + \left(\frac{\frac{Vicm - 12V}{CMRR}}{Rshunt.I}\right)^2 + \left(\frac{Vref.(\varepsilon ref)}{G.Rshunt.I}\right)^2}$$
(14)



Note that the input bias currents are not considered in this section, as it has been considered that this current is already integrated in the Vsense. The TSC2020 cannot measure current in the same order as input bias current (several hundreds of μ A).

Linearity is not considered in the error calculus as it represents only 0.01% of error and is negligible. Nevertheless, as the gain error has been calculated thanks to the best-fit line approach, it gives the information that the gain error can be relatively constant throughout the linear input range of the TSC2020.

Equation 15 has been described for a temperature of 25 °C. With temperature variation, the DV_{IO}/DT error term must certainly be added. And if the power supply is susceptible to change, the SVR parameter must also be considered. For more information about the expected error on a current sensing output you can refer to the application note AN5849. The shunt accuracy must also be taken into consideration.

Example

Let us take an example to get a better understanding of the maximum total error that can happen on the output of the TSC2020 (x20).

Use case:

- V_{CC} = 5 V
- V_{icm} = 24 V
- V_{ocm} = 2.5 V
- Temperature = 25 °C
- I_{load} = 10 A
- Shunt 5 mΩ

Theoretically, the expected output voltage should be $V_{out} = R_{shunt} * I_{load} * 20 + V_{ocm} = 3.5 V.$

From the above equations, let us detail all the error terms by using the maximum value of the electrical characteristic (when available). The % error on output in the following table is expressed in reference of $V_{out} - V_{ref}$, so in this typical example: 1 V.

Error source	Calculus	Output voltage error	% error on output
Gain error	$20*5.10^{-3}*10*0.3\%$	3 mV	0.3%
Vio error	20*150µV	3 mV	0.3%
CMRR error	$20^* \frac{24V - 12V}{10^{\frac{100}{20}}}$	2.4 mV	0.2%
Vocm error	2.5*0.2%	5 mV	0.5%
Noise	$20^* \frac{53nV}{\sqrt{Hz}} \sqrt{700kHz^* \frac{\pi}{2} - 0.1Hz}$	1.1 mVrms	0.3% (1)

1. The percentage is based on the voltage peak value and is 3 times the RMS value.

An error of 0.75% can be expected on the output of the TSC2020 @ 25 °C for a current of 10 A flowing.





5.8 Input filtering

Although the TSC2020 does not require input filtering for good accuracy measurement, depending on application requirements a low-pass filter may be needed. In this case it is always better to filter the TSC2020 output rather than the input pins. Anyway, the TSC2020 output shows a low impedance even in high frequency shown in Figure 61. Zout vs. frequency, and adding an output filter certainly acts to increase the output impedance.



Adding resistances on the input pins creates an impedance mismatch with the internal bias block, which allows to correctly polarize the input stage when the common mode voltage is higher than the power supply voltage. The block diagram is described in Figure 62. Input filter.

Figure 62. Input filter



When an input differential voltage is applied, this bias block presents a differential impedance of 1.4 k Ω as described by Figure 63. Differential input impedance. This mismatch has a direct impact on the gain accuracy, as described by equation 16.

$$Gain\,error = 1 - \frac{700}{Rs + 700}\tag{15}$$

Figure 61. Zout vs. frequency



In a second order due to the mismatch of the external serial resistance, an input offset voltage may also be added as depicted by equation 17:

Input Offset voltage =
$$Rs \cdot 2 \cdot \epsilon \alpha \cdot (lib)$$
 (16)

Where $\epsilon \alpha$ is the resistance precision.

In order to limit error, it is advised to use serial resistance as low as possible on the input. 10 Ω or lower could be a good value.

By using a serial resistance of 10 Ω (±1%) on the input pins of the TSC2020 in a 48 V application (corresponding to an lib = 200 μ A), a gain error of 1.4% can appear and an added input offset of 40 μ V.



5.9 Stability

Driving large capacitive Cload can produce gain peaking in the frequency response, with overshoot and ringing in the step response. In order to smooth the output, a serial resistance Riso can be inserted between the TSC2020 output and the capacitive load as depicted by Figure 64. Serial resistance Riso.

Figure 64. Serial resistance Riso



The criteria chosen to ensure the stability of the system is an overshoot lower than 24% to a small input step voltage. Figure 65. Stability criteria overshoot 24% shows the TSC2020 output response, loaded with 680 pF capacitor, to a 5 mV input step. It depicts the stability criteria acceptance with an overshoot lower than 24%.

Figure 65. Stability criteria overshoot 24%



Time (Tuµs/div)

For load capacitance higher than 680 pF, and in order to respect an overshoot lower than 24%, and expecting an output signal as the one in Figure 65. Stability criteria overshoot 24%, a serial resistor must be added to the output, as described in Figure 66. Stability criteria with a serial resistor at V_{CC} = 5 V.



Figure 66. Stability criteria with a serial resistor at V_{CC} = 5 V



5.10 Low distortion

The TSC2020 demonstrates a low level of distortion especially in low frequency. Figure 67. THD+N shows an optimum accuracy in the 10 kHz bandwidth. It remains good less than 1% in the bandwidth range of the TSC2020.

Figure 67. THD+N





5.11 Power supply recommendation

In order to correctly decouple the TSC202x, it is recommended to place a 100 nF bypass capacitor between Vcc and Gnd. This capacitor must be placed as close as possible to the supply pins. Figure 68. Startup time with a decoupling capacitance of 100 nF shows a startup time with a decoupling capacitance of 100 nF.



Figure 68. Startup time with a decoupling capacitance of 100 nF

It is also important to take into consideration the V_{ref} pin, which is used to fix the output common mode voltage. Effectively, this pin must be driven by a low impedance voltage source and can be decoupled thanks to a 10 nF bypass capacitor.

A larger bypass capacitor added on the V_{CC} pin and V_{ref} pin should help to enhance CMRR and PSRR performance.



5.12 PCB layout recommendations

Particular attention must be paid to the layout of the PCB tracks connected to the current sensing, load, and power supply. It is good practice to use short and wide PCB traces to minimize voltage drops and parasitic inductance.

When using shunt resistance lower than 1 Ω , it is important to use a 4-wire connection technique to sense the current, as described in the schematic below. Effectively, this technique allows to separate pairs of current-carrying and voltage-sensing electrodes to make more accurate measurements by eliminating the lead and contact resistance from the measurement.

It is also important to treat the track connected to the input pin of the TSC202x as a differential pair; it must have the same length and width, ideally placed on the same PCB plane, and above all must be routed as far as possible from noisy sources. As this track carries the input bias current, in a range of hundreds of μ A, it can be designed small but always by taking care of its resistivity. Any vias in these input tracks are not recommended to avoid any parasitic resistance in this path.

To minimize parasitic impedance over the entire surface, a multi-via technique that connects the bottom and top layer ground planes together in many locations is often used.

A ground plane generally helps to reduce EMI, which is why it is generally recommended to use a multilayer PCB and use the ground planes as a shield to protect the internal track. In this case, pay attention to separate the digital from the analog ground and avoid any ground loop. To minimize EMI impact, it is important to reduce the loop area or antenna.

Figure 69. Recommended layout suggests a possible routing for the TSC202x in order to minimize as much as possible parasitic effect.



Figure 69. Recommended layout

5.13 Application examples

Inline motor control application

The configuration described in Figure 70. Inline motor control application schematic, inline phase current sensing is the best method to precisely know the phase current flowing into the motor. This current measurement offers the best information that can be used in feedback motor control, to optimize the motor performance. The main advantage of this topology is that the current can be read without a strong linkage to the PWM status and without timing limitations in case of very small PWM applied to the phase (low-side current sensing can only be executed while the low-side transistor of that leg is on). It also allows the detection of phase short-circuits.



Figure 70. Inline motor control application schematic

As the shunt resistance is placed directly in line with the PWM driver, the input pins of the TSC202x can see in few nanoseconds several tens of volt, depending on the motor to drive. As demonstrated in Figure 71. TSC2020 used in inline topology, the TSC2020 can limit the unwanted disturbance on the output and offer a stable output in few µs after a common mode transient.

The TSC2020 is a bidirectional high-side current sensing especially designed for this kind of application and offers optimized performance.

Figure 71. TSC2020 used in inline topology



Time (10µs/div)



6 Package information

To meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.



6.1 SO8 package information

Figure 72. SO8 package outline





Table 6. SO8 package mechanical data

	Dimensions						
Ref.	Millimeters			Inches			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А			1.75			0.069	
A1	0.10		0.25	0.04		0.010	
A2	1.25			0.049			
b	0.28	0.40	0.48	0.011	0.016	0.019	
С	0.17		0.23	0.007		0.010	
D	4.80	4.90	5.00	0.189	0.193	0.197	
E	5.80	6.00	6.20	0.228	0.236	0.244	
E1	3.80	3.90	4.00	0.150	0.154	0.157	
е		1.27			0.050		
h	0.25		0.50	0.010		0.020	
L	0.40	0.635	1.27	0.016		0.050	
L1		1.04			0.040		
k	1°		8°	1°		8°	
ссс			0.10			0.004	



Figure 73. SO8 recommended footprint





6.2 MiniSO8 package information



Table 7. MiniSO8 mechanical data

	Dimensions						
Ref.	Millimeters			Inches			
	Min.	Тур.	Max.	Min.	Тур.	Max.	
А			1.1			0.043	
A1	0		0.15	0		0.006	
A2	0.75	0.85	0.95	0.03	0.033	0.037	
b	0.22		0.4	0.009		0.016	
с	0.08		0.23	0.003		0.009	
D	2.8	3	3.2	0.11	0.118	0.126	
E	4.65	4.9	5.15	0.183	0.193	0.203	
E1	2.8	3	3.1	0.11	0.118	0.122	
е		0.65			0.026		
L	0.4	0.6	0.8	0.016	0.024	0.031	
L1		0.95			0.037		
L2		0.25			0.01		
k	0°		8°	0°		8°	
CCC			0.1			0.004	

Figure 75. MiniSO8 recommended footprint





6.3 TSSOP8 package information





Table 8. TSSOP8 mechanical data

	Dimensions					
Ref.	Millimeters			Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.
A	-	-	1.20			0.047
A1	0.05	-	0.15	0.002		0.006
A2	0.90	1.00	1.05	0.035	0.039	0.041
A3	0.39	0.44	0.49	0.015	0.017	0.019
b	0.20	-	0.28	0.008	-	0.011
b1	0.19	0.22	0.25	0.007	0.008	0.010
D2	3.55	3.65	3.75	0.140	0.144	0.148
С	0.13	-	0.17	0.005	-	0.007
c1	0.12	0.13	0.14	0.005	0.005	0.006
D	2.90	3.00	3.10	0.114	0.118	0.122
E1	4.30	4.40	4.50	0.169	0.173	0.177
E	6.20	6.40	6.60	0.244	0.252	0.260
е	0.65 BSC			0.025 BSC		
L	0.45	-	0.75	0.018	-	0.030
L1	1.00 REF			0.039 REF		
θ	0°	-	8°	0°	-	8°

Figure 77. TSSOP8 recommended footprint





7 Ordering information

Table 9. Order codes				
Order code	Gain (V/V)	Package	Packaging	Marking
TSC2020IDT	20	SO8		TSC2020
TSC2020IYDT (1)			Tape & Reel	TSC2020Y
TSC2020IST		MiniSO8		O129
TSC2020IYST (1)				O132
TSC2020IPT		TSSOP8		O129
TSC2020IYPT (1)				O132
TSC2021IDT	50	SO8		TSC2021
TSC2021IYDT ⁽¹⁾				TSC2021Y
TSC2021IST		MiniSO8		O130
TSC2021IYST ⁽¹⁾				O133
TSC2021IPT		TSSOP8		O130
TSC2021IYPT ⁽¹⁾				O133
TSC2022IDT		SO8 50 MiniSO8 TSSOP8 SO8 100 MiniSO8		TSC2022
TSC2022IYDT ⁽¹⁾				TSC2022Y
TSC2022IST	- 100	MiniSO8		O131
TSC2022IYST ⁽¹⁾				O134
TSC2022IPT		T000D0		O131
TSC2022IYPT ⁽¹⁾		133050		O134

1. Qualified and characterized according to AEC Q100 and Q003 or equivalent, advanced screening according to AEC Q001 & Q002 or equivalent.

Revision history

Table 10. Document revision history

Date	Revision	Changes
22-Sep-2023	1	Initial release.
20-May-2024	2	Added new TSC2021 and TSC2022 order codes in Table 8.
02-Jul-2024	3	Updated RT condition, Acc parameter in Table 4 and
		Section 4: Typical characteristics.
11-Oct-2024	4	Added new package TSSOP8, Section 5: Application information and Section 6.3: TSSOP8 package information.
		Updated Section 1 and Table 9. Order codes.
21-Oct-2024	5	Updated ESD value for TSSOP8 in Table 2.
		Minor text changes.



Contents

1	Block	diagram and pin description		
2	Abso	lute maximum ratings and operation conditions		
3	Elect	rical characteristics4		
4	Typical characteristics			
5	Appli	cation information		
	5.1	Overview		
	5.2	Theory of operation		
	5.3	PWM enhancer		
	5.4	Unidirectional / bidirectional operation		
	5.5	RSENSE selection		
	5.6	Input offset voltage drift over temperature24		
	5.7	Error calculation		
	5.8	Input filtering		
	5.9	Stability		
	5.10	Low distortion		
	5.11	Power supply recommendation		
	5.12	PCB layout recommendations		
	5.13	Application examples		
6	Pack	age information		
	6.1	SO8 package information		
	6.2	MiniSO8 package information		
	6.3	TSSOP8 package information		
7	Orde	ring information		
Rev	ision h	nistory		



List of tables

Table 1.	Pin description.	2
Table 2.	Absolute maximum ratings	3
Table 3.	Operating conditions	3
Table 4.	Electrical characteristics - V _{CC} = 2.7 V, V _{ICM} = 48 V, T = 25 °C (unless otherwise specified)	4
Table 5.	Electrical characteristics - V _{CC} = 5 V, V _{ICM} = 48 V, T = 25 °C (unless otherwise specified).	6
Table 6.	SO8 package mechanical data	6
Table 7.	MiniSO8 mechanical data	8
Table 8.	TSSOP8 mechanical data	0
Table 9.	Order codes	2
Table 10.	Document revision history	.3



List of figures

Figure 1.	Block diagram	. 2
Figure 2.	Pin connections (top view)	. 2
Figure 3.	Input offset production distribution	. 8
Figure 4.	Gain error production distribution	. 8
Figure 5.	Common-mode rejection ratio production distribution.	. 8
Figure 6.	Supply current vs. supply voltage	. 8
Figure 7.	Supply current vs. input common-mode	. 9
Figure 8.	Supply current vs. temperature	. 9
Figure 9.	Input bias current vs. input common-mode	. 9
Figure 10.	Input bias current vs. temperature	. 9
Figure 11.	Input bias current vs. input common-mode	. 9
Figure 12.	Input bias current vs. Vsense	. 9
Figure 13.	Input offset voltage vs. temperature	10
Figure 14.	Input offset voltage vs. input common-mode with V_{CC} = 5.5 V	10
Figure 15.	Input offset voltage vs. input common-mode with V _{CC} = 2.7 V	10
Figure 16.	Input offset voltage vs. supply voltage	10
Figure 17.	Output current vs. output voltage	11
Figure 18.	Output current vs. temperature with V _{CC} = 5.5 V	11
Figure 19.	Output current vs. temperature with V _{CC} = 2.7 V	11
Figure 20.	V_{ob} and V_{ol} vs. temperature with V_{CC} = 5.5 V	11
Figure 21.	V_{ob} and V_{ol} vs. temperature with $V_{cc} = 2.7 V$	11
Figure 22	Linearity vs. Vsense with $V_{cc} = 5.5$ V	11
Figure 23	Linearity vs. Vsense	12
Figure 24.	Gain error vs. input common-mode different V _{CC}	12
Figure 25	Gain error vs. input common-mode voltage different temperature	12
Figure 26.	Load regulation with $V_{cc} = 5 V$	12
Figure 27	Gain vs. frequency	13
Figure 28.	Gain vs. frequency with different capacitive load	13
Figure 29.	Gain vs. frequency with different capacitive load (TSC2021)	13
Figure 30.	Gain vs. frequency with different capacitive load (TSC2022)	13
Figure 31.	Bandwidth vs. input common-mode	14
Figure 32.	Overshoot vs. capacitive load	14
Figure 33.	Small signal response with $V_{CC} = 5 V$	14
Figure 34.	Large signal response with $V_{CC} = 5 V$	14
Figure 35.	Large signal response with $V_{CC} = 5 V (TSC2021)$	14
Figure 36	Large signal response with $V_{co} = 5 V$ (TSC2022)	14
Figure 37	Positive settling time 1% vs. input common mode	15
Figure 38	Negative settling time 1% vs. input common-mode	15
Figure 39	48 V common-mode positive step response recovery	15
Figure 40	48 V common-mode pegative step response recovery	15
Figure 41	100 V common-mode positive step response recovery	16
Figure 42	100 V common-mode negative step response recovery	16
Figure 43.	PSRR vs. frequency	16
Figure 44.	CMRR vs. frequency	16
Figure 45.	Positive overvoltage recovery.	16
Figure 46.	Negative overvoltage recovery	16
Figure 47.	Overvoltage recovery vs input common-mode, $V_{CC} = 5 V$.	17
Figure 48.	Noise vs. frequency.	17
Figure 49.	0.1 Hz to 10 Hz voltage noise.	17
Figure 50.	Power up time delay	17
Figure 51.	Output impedance vs. frequency.	17



TSC2020, TSC2021, TSC2022 List of figures

Figure 52.	Functional block diagram	18
Figure 53.	Output response to large $\Delta V/\Delta T$ input common mode signals	19
Figure 54.	Output referenced to ground.	20
Figure 55.	Output referenced to V _{CC} .	21
Figure 56.	Split supply	21
Figure 57.	External supply.	22
Figure 58.	Recommended schematic	22
Figure 59.	Tradeoff between shunt resistance, power dissipation, and accuracy	23
Figure 60.	Schematic for V _{ocm} error	25
Figure 61.	Zout vs. frequency	27
Figure 62.	Input filter.	27
Figure 63.	Differential input impedance	28
Figure 64.	Serial resistance Riso	29
Figure 65.	Stability criteria overshoot 24%	29
Figure 66.	Stability criteria with a serial resistor at V _{CC} = 5 V	30
Figure 67.	THD+N	30
Figure 68.	Startup time with a decoupling capacitance of 100 nF	31
Figure 69.	Recommended layout	32
Figure 70.	Inline motor control application schematic	33
Figure 71.	TSC2020 used in inline topology.	34
Figure 72.	SO8 package outline	36
Figure 73.	SO8 recommended footprint.	37
Figure 74.	MiniSO8 package outline	38
Figure 75.	MiniSO8 recommended footprint.	39
Figure 76.	TSSOP8 package outline	40
Figure 77.	TSSOP8 recommended footprint	41



IMPORTANT NOTICE - READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2024 STMicroelectronics – All rights reserved